



75648001



### Universal input/output interface 8gang KNX

#### Technical Features

##### Settings

Supported configuration mode	ETS
------------------------------	-----

##### Electric current

Number of entry circuits	8
--------------------------	---

##### Equipment

External signal voltage necessary	No
-----------------------------------	----

##### Connectivity

With bus system KNX radio	No
---------------------------	----

##### Equipment

Radio frequency bidirectional	No
-------------------------------	----

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Lighting

LED controlling	Yes
-----------------	-----

##### Materials

Colour	Black
RAL code	9005

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

##### Cable

Cable length	10 m
--------------	------

##### Voltage

Input voltage	20 - 20 V
Operating voltage over bus	21 - 32 V
Type voltage supply	AC/DC

##### Dimensions

Height	48 mm
Depth	32 mm

##### Texts

Type of connection	With screw terminals
--------------------	----------------------

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes