



BD363N

Earth leakage add-on block 3P 63A 30mA A Class

Technical Features

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	30 mA
Rated current	63 A

Architecture

Number of poles	3
Neutral position	Right

Capacity

Number of modules	3
-------------------	---

Installation, mounting

Nominal tightening torque	2.90 - 2.90 Nm
Nominal tightening torque down terminal	2.90 - 2.90 Nm

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	70 mm
Width	44 mm
Depth	92 mm