



KH45A

Main line branch terminal 5pole, 2x35mm²-2x25mm² per pole, IP20, 3x L, 1xE, 1xN

Technical Features

Dimensions

Height	38 mm
Width	135 mm
Depth	53 mm

Connection

Cross-section rigid conductor	1.5 - 35 mm ²
-------------------------------	--------------------------

Installation, mounting

Nominal tightening torque	3.50 - 3.50 Nm
---------------------------	----------------

Electric current

Rated current	100 A
---------------	-------

Architecture

Number of poles	5
-----------------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes