



ATA205008014

**Trunking 20x50,L=2,0m,brown**

**Technical Features**

**Dimensions**

|                     |                           |
|---------------------|---------------------------|
| Height              | 20 mm                     |
| Width               | 52 mm                     |
| Length              | 2000 mm                   |
| Inner cross-section | 900 - 900 mm <sup>2</sup> |

**Capacity**

|  |   |
|--|---|
| Max. number of cables (Ø11mm, 50% filled, without devices) | 5 |
|--|---|

**Materials**

|           |                         |
|-----------|-------------------------|
| Material  | Polyvinylchloride (PVC) |
| Treatment | Untreated               |
| RAL code  | 8014                    |
| Colour    | Brown                   |

**Safety**

|                               |      |
|-------------------------------|------|
| Impact resistance IK          | IK07 |
| Ingress Protection (IP) class | IP40 |

**Standards**

|   |    |
|---|----|
| Suitable for functional integrity according to DIN4102-12 | No |
|---|----|

**Use conditions**

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 65 °C |
|-----------------------|------------|

**Connectivity**

|                   |                  |
|-------------------|------------------|
| Trunking coupling | Without coupling |
|-------------------|------------------|

**Equipment**

|                                |     |
|--------------------------------|-----|
| Number of partitions           | 0   |
| Number of pluggable partitions | 0   |
| Cable retaining clip included  | Yes |
| With protective film           | No  |

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |