



ATA205008014

Trunking 20x50,L=2,0m,brown

Technical Features

Dimensions

| | |
|---------------------|---------------------------|
| Height | 20 mm |
| Width | 52 mm |
| Length | 2000 mm |
| Inner cross-section | 900 - 900 mm ² |

Capacity

| | |
|--|---|
| Max. number of cables (Ø11mm, 50% filled, without devices) | 5 |
|--|---|

Materials

| | |
|-----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
| Treatment | Untreated |
| RAL code | 8014 |
| Colour | Brown |

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |

Standards

| | |
|---|----|
| Suitable for functional integrity according to DIN4102-12 | No |
|---|----|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 65 °C |
|-----------------------|------------|

Connectivity

| | |
|-------------------|------------------|
| Trunking coupling | Without coupling |
|-------------------|------------------|

Equipment

| | |
|--------------------------------|-----|
| Number of partitions | 0 |
| Number of pluggable partitions | 0 |
| Cable retaining clip included | Yes |
| With protective film | No |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |