



JK129AG

JK A Board 2 Row Glazed Door

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	Yes
----------------------------	-----

Overvoltage protection	No
------------------------	----

Capacity

Number of modules	29
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	107.70 mm
-------	-----------

Height	450 mm
--------	--------

Width	465 mm
-------	--------

Cover, door

Interlockable	No
---------------	----

Door/cover is transparent	Yes
---------------------------	-----

Materials

RAL code	7035
----------	------

Colour	Light grey
--------	------------

Material	Steel
----------	-------

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Equipment

Number of rows	2
----------------	---

Number of rails	2
-----------------	---

Safety

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

Protection class	Isolation class I
------------------	-------------------

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----