



JK129AG

JK A Board 2 Row Glazed Door

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	Yes
Overvoltage protection	No

Capacity

Number of modules	29
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	107.70 mm
Height	450 mm
Width	465 mm

Cover, door

Interlockable	No
Door/cover is transparent	Yes

Materials

RAL code	7035
Colour	Light grey
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	0
-----------------------------	---

Equipment

Number of rows	2
Number of rails	2
With socket outlet	No

Safety

Ingress Protection (IP) class	IP2XC
Protection class	Isolation class I
Number of earth leakage switches 300 mA	0

Sustainability

RoHS conform	Yes
--------------	-----