

Technical Features

Dimensions

Height	275 mm
Width	445 mm
Depth	125 mm
Thickness of sidewall	1.20 mm

Safety

Ingress Protection (IP) class	IP41
Protection class	Isolation class I
Locking type	Special tool Without lock
Impact resistance IK	IK05

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Materials

Colour	Grey white
RAL code	9002
Treatment	Varnished
Material	Steel

Equipment

Number of rows	1
----------------	---

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No

Sustainability

RoHS conform	Yes
--------------	-----