



JK1E16S

Technical Features

Dimensions

| | |
|-----------------------|---------|
| Height | 275 mm |
| Width | 445 mm |
| Depth | 125 mm |
| Thickness of sidewall | 1.20 mm |

Safety

| | |
|-------------------------------|------------------------------|
| Ingress Protection (IP) class | IP41 |
| Protection class | Isolation class I |
| Locking type | Special tool Without lock |
| Impact resistance IK | IK05 |

Equipment

| | |
|---------------------------------|---|
| Number of flange plate openings | 2 |
|---------------------------------|---|

Installation, mounting

| | |
|----------------------------|------------------|
| Mounting on | Surface mounting |
| Suitable for outdoor usage | No |

Materials

| | |
|-----------|------------|
| Colour | Grey white |
| RAL code | 9002 |
| Treatment | Varnished |
| Material | Steel |

Equipment

| | |
|----------------|---|
| Number of rows | 1 |
|----------------|---|

Cover, door

| | |
|---------------------------|----|
| Number of cabinet doors | 1 |
| Door/cover is transparent | No |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |