



EEA001A

External dimmer 500W for IP Roombox

Technical Features

Voltage

Rated operational voltage U _e	230 - 230 V
--	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	White
RAL code	9001
Material	Thermoplastic

Dimensions

Height	85 mm
Depth	62 mm

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Power

Power incandescent lamp	500 - 500 W
-------------------------	-------------

Use conditions

Operating temperature	-20 - 50 °C
-----------------------	-------------

Capacity

Number of modules	2
-------------------	---

Texts

Dimming principle	Automatic setting of load-dependent switching principle (autodetect process)
Type of connection	With screw terminals