



EEA001A

External dimmer 500W for IP Roombox

Technical Features

Voltage

Rated operational voltage Ue 230 - 230 V

Frequency

Frequency 50 - 60 Hz

Materials

Colour White

RAL code 9001

Material Thermoplastic

Dimensions

Height 85 mm

Depth 62 mm

Architecture

Control/operation element Single push button

Power

Power incandescent lamp 500 - 500 W

Use conditions

Operating temperature -20 - 50 °C

Capacity

Number of modules 2

Texts

Dimming principle Automatic setting of load-dependent switching principle (autodetect process)

Type of connection With screw terminals