



LFS601500VERZ

**Trunking LFS made of steel 60x150mm galvanized**

**Technical Features**

**Dimensions**

Height	60 mm
Width	150 mm
Length	2000 mm
Inner cross-section	7000 - 7000 mm <sup>2</sup>

**Capacity**

Max. number of cables (Ø11mm, 50% filled, without devices)	29
--	----

**Materials**

Material	Steel
Treatment	Galvanised
Colour	Zinc

**Safety**

Impact resistance IK	IK08
Ingress Protection (IP) class	IP30

**Standards**

Suitable for functional integrity according to DIN4102-12	No
---	----

**Use conditions**

Operating temperature	-5 - 90 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

**Equipment**

Number of partitions	0
Number of compartments	1 - 3
Number of pluggable partitions	2
Cable retaining clip included	Yes
With protective film	No

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

**Illustrations | Drawings**

