



FL302B

**Polyester wall mounting enclosure, Orion.Plus, plain door 1150x600x300 mm**

**Technical Features**

**Dimensions**

Height	1150 mm
Width	600 mm
Depth	300 mm
Thickness of sidewall	2 mm

**Safety**

Ingress Protection (IP) class	IP65
Protection class	Isolation class II
Locking type	Barrel lock Key lock
Impact resistance IK	IK10

**Equipment**

Number of section in width	1
Number of flange plate openings	0

**Installation, mounting**

Mounting on	Wall mounting
Suitable for outdoor usage	Yes

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester

**Equipment**

Number of rows	7
----------------	---

**Cover, door**

Number of cabinet doors	2
Door/cover is transparent	No

**Electric current**

Rated current	630 A
---------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----