



28342089

Rot. dimmer centre plate (R, L, C), soft-lock, R.classic, p. white glossy

Technical Features

Voltage

Operating voltage	230 - 230 V
-------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Polar white
RAL code	9010
Material	Metal Plastic

Dimensions

Diameter axis	4 mm
Height	71 mm
Width	71 mm
Depth	59 mm

Architecture

Control/operation element	Push & rotative switch
---------------------------	------------------------

Use conditions

Operating temperature	5 - 25 °C
-----------------------	-----------

Texts

Dimming principle	Phase cut-on or cut-off according to load type, self-learning
Fuse	Short-circuit and overload-proof (electronic fuse)
Voltage	Voltage test possible without dismantling
Installation mode	For screw fastening
Type of connection	With plug-in terminals
Extension unit input	With input for extension units insert for universal rotary dimmer