



VU12NSG

Encl.,Volta,flush,1x12MOD,IP30,Version Singapore

Technical Features

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

Electric current

Rated current	63 A
---------------	------

Power

Maximum power loss per cabinet at $\Delta T=20K$	12 W
--	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

Capacity

Number of modules	12
Number of half modules terminals per rail	24

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	356 mm
Width	348 mm
Depth	94.50 mm
Built-in height	340 mm
Built-in width	335 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Built-in depth	90 mm
----------------	-------

Cover, door

Number of locks	0
-----------------	---

Dimensions

Number of width units	12
-----------------------	----

Cover, door

Door/cover is transparent	No
---------------------------	----

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Plastic
RAL code	9010
Colour	Pure white

Equipment

Has earthing terminal block	Yes
Has mounting plate	No

Materials	
Ultraviolet-resistant	Yes
Safety	
Protection class	Isolation class II
Ingress Protection (IP) class	IP30
Locking type	Snap on lock Without lock
Glow wire test	650 °C
Sustainability	
RoHS conform	Yes