



LFF4006009016

Trunking LFF 40x57mm with coupling and 2 cable clips traffic white

Technical Features

Dimensions

| | |
|---------------------|-----------------------------|
| Height | 40 mm |
| Width | 57 mm |
| Length | 2000 mm |
| Inner cross-section | 1500 - 1500 mm ² |

Capacity

| | |
|--|---|
| Max. number of cables (Ø11mm, 50% filled, without devices) | 7 |
|--|---|

Materials

| | |
|-----------|-------------------------|
| Material | Polyvinylchloride (PVC) |
| Treatment | Untreated |
| RAL code | 9016 |
| Colour | Traffic white |

Safety

| | |
|-------------------------------|------|
| Impact resistance IK | IK07 |
| Ingress Protection (IP) class | IP40 |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5 - 60 °C |
|-----------------------|------------|

Connectivity

| | |
|-------------------|----------------------------|
| Trunking coupling | Pre-equipped with couplers |
|-------------------|----------------------------|

Equipment

| | |
|--------------------------------|-----|
| Number of partitions | 0 |
| Number of pluggable partitions | 0 |
| Cable retaining clip included | Yes |
| With protective film | No |

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |