



JK104BDFG

JK112 64 Module Side DIN Rail Box Glazed

Technical Features

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rows	4
With lock	Yes
Has neutral terminal block	Yes

Capacity

Number of modules	64
-------------------	----

Dimensions

Height	850 mm
Width	465 mm
Depth	132.50 mm

Cover, door

Number of cabinet doors	1
-------------------------	---

Dimensions

Number of width units	64
-----------------------	----

Cover, door

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Equipment

Has earthing terminal block	Yes
-----------------------------	-----

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock Quarter turn lock

Sustainability

RoHS conform	Yes
--------------	-----