



JK104BDFG

### JK112 64 Module Side DIN Rail Box Glazed

#### Technical Features

##### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

##### Electric current

Rated current	125 A
---------------	-------

##### Equipment

Number of rows	4
With lock	Yes
Has neutral terminal block	Yes

##### Capacity

Number of modules	64
-------------------	----

##### Dimensions

Height	850 mm
Width	465 mm
Depth	132.50 mm

##### Cover, door

Number of cabinet doors	1
-------------------------	---

##### Dimensions

Number of width units	64
-----------------------	----

##### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

##### Materials

Material	Steel
RAL code	7035
Colour	Light grey

##### Equipment

Has earthing terminal block	Yes
-----------------------------	-----

##### Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock Quarter turn lock

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes