



HTG911H

**Power supply 24V DC 2,5A at 70°C**

**Technical Features**

**Electric current**

Output current	2500 mA
Intensity output 1	2.50 A

**Functions**

Output voltage adjusted	No
-------------------------	----

**Frequency**

Frequency	47 - 63 Hz
-----------	------------

**Power**

Power consumption standby	0.3 W
---------------------------	-------

**Connection**

Connector/plug type	Screw terminal
---------------------	----------------

**Capacity**

Number of modules	4
-------------------	---

**Voltage**

Output voltage	23.28 - 24.72 V
----------------	-----------------

**Use conditions**

Operating temperature	-10 - 70 °C
-----------------------	-------------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Dimensions**

Height	93 mm
Width	71 mm
Depth	63 mm

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes