



HTG911H

Power supply 24V DC 2,5A at 70°C

Technical Features

Electric current

Output current	2500 mA
Intensity output 1	2.50 A

Functions

Output voltage adjusted	No
-------------------------	----

Frequency

Frequency	47 - 63 Hz
-----------	------------

Power

Power consumption standby	0.3 W
---------------------------	-------

Connection

Connector/plug type	Screw terminal
---------------------	----------------

Capacity

Number of modules	4
-------------------	---

Voltage

Output voltage	23.28 - 24.72 V
----------------	-----------------

Use conditions

Operating temperature	-10 - 70 °C
-----------------------	-------------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Dimensions

Height	93 mm
Width	71 mm
Depth	63 mm

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes