



HTG911H

Power supply 24V DC 2,5A at 70°C

Technical Features

Electric current

| | |
|--------------------|---------|
| Output current | 2500 mA |
| Intensity output 1 | 2.50 A |

Functions

| | |
|-------------------------|----|
| Output voltage adjusted | No |
|-------------------------|----|

Frequency

| | |
|-----------|------------|
| Frequency | 47 - 63 Hz |
|-----------|------------|

Power

| | |
|---------------------------|-------|
| Power consumption standby | 0.3 W |
|---------------------------|-------|

Connection

| | |
|---------------------|----------------|
| Connector/plug type | Screw terminal |
|---------------------|----------------|

Capacity

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Voltage

| | |
|----------------|-----------------|
| Output voltage | 23.28 - 24.72 V |
|----------------|-----------------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 70 °C |
|-----------------------|-------------|

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Dimensions

| | |
|--------|-------|
| Height | 93 mm |
| Width | 71 mm |
| Depth | 63 mm |

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |