



HI460

Change-over switch 4P 800A

Technical Features

Voltage

Rated insulation voltage U_i	1000 V
Rated impulse withstand voltage U_{imp}	12000 V

Electric current

Rated current	800 A
Rated short-time withstand current I_{cw} IEC 60947	64 kA
Rated conditional short-circuit current I_{cc} with gl-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	526000 W
--------------------------------------------	----------

Architecture

Number of poles	4
Control/operation element	Long rotary handle
Type of pole	4P

Dimensions

Height	321 mm
Width	466 mm
Depth	375 mm

Controls and indicators

Motor drive integrated	No
------------------------	----

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Total power loss under IN	166.80 W
---------------------------	----------

Connection

Cross-section rigid conductor	4x 185 mm ²
-------------------------------	------------------------