



16406096

Relay switch centre plate for hotel card, Q.x, ant. velvety, lacq.

#### Technical Features

##### Electric current

Switching current	10 A
Momentary contact current	10 A

##### Voltage

Rated voltage	230 V
---------------	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Architecture

Control/operation element	Hotel card
Number of poles	1

##### Power

230 V incandescent and halogen lamp	1500 W
Fluorescent lamps in duo circuit	1500 W

##### Materials

Colour	Anthracite
Surface finish	Velvety
Material	Metal Plastic
Treatment	Varnished
Transparent	No

##### Dimensions

Height	71 mm
Width	71 mm
Depth	57.30 mm
Built-in depth	32 mm
Built-in depth flush-mounted boxes	35 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Controls and indicators

Number of buttons	0
With feedback signal contact	No

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Operating temperature	-5 - 50 °C
-----------------------	------------

##### Texts

Imprint	With imprint "Hotelcard"
Installation mode	With spreader claws
Lighting	For illumination
Switch mode	1-pole
Type of connection	With screw-in lift terminals

##### Suitable for

Q.x	
-----	--

##### Sustainability

RoHS conform	Yes
--------------	-----