



50463522



Push-button insert,change-over contact,illuminated surf.-/flushmtd,W.1,p.wh.

Technical Features

Electric current

Momentary contact current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Rocker

Materials

Colour Polar white

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

Dimensions

Height 71 mm

Width 71 mm

Depth 43 mm

Built-in depth flush-mounted boxes 0 mm

Installation, mounting

Mounting on Flush mounting
Surface mounting

Controls and indicators

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

Safety

Ingress Protection (IP) class IP55

Impact resistance IK IK05

Accessories

Has labelling field No

Use conditions

Operating temperature -25 - 35 °C

Texts

Imprint Without imprint

Installation mode For screw fastening

Lighting With blue 230 V LED unit
For lighting and monitoring circuit

Type of connection With N-terminal
With plug-in terminals