



50463522

Push-button insert,change-over contact,illuminated surf.-/flushmtd,W.1,p.wh.

### Technical Features

#### Electric current

Momentary contact current	10 A
---------------------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Architecture

Control/operation element	Rocker
---------------------------	--------

#### Materials

Colour	Polar white
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

#### Dimensions

Height	71 mm
Width	71 mm
Depth	43 mm
Built-in depth flush-mounted boxes	0 mm

#### Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

#### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

#### Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

#### Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

#### Texts

Imprint	Without imprint
Installation mode	For screw fastening
Lighting	With blue 230 V LED unit For lighting and monitoring circuit
Type of connection	With N-terminal With plug-in terminals