



WMMTVF



Single IEC Female Euromodule White

Technical Features

Connectivity

| | |
|---------------|------------------|
| Mounting type | Snap-on mounting |
|---------------|------------------|

Attenuation

| | |
|---------------------|---------|
| Tap loss at 860 MHz | 0.30 dB |
|---------------------|---------|

Connection

| | |
|---------------------|---------------|
| Connector/plug type | Direct socket |
|---------------------|---------------|

Frequency

| | |
|---------------------|-------------|
| Frequency bandwidth | 5 - 860 MHz |
|---------------------|-------------|

Equipment

| | |
|-------------------|---|
| Number of outputs | 1 |
|-------------------|---|

Materials

| | |
|----------|-------------------|
| Material | Urea formaldehyde |
| Colour | White |

Dimensions

| | |
|-------|-------|
| Depth | 24 mm |
|-------|-------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |