

Change-over switch 4P 400A w/ ext handle and bridging bars India

Technical Features

Voltage

Rated operational voltage Ue	380 - 690 V
Rated insulation voltage Ui	1000 V
Rated impulse withstand voltage Uimp	12000 V

Electric current

Rated current	400 A
Rated short-time withstand current Icw IEC 60947	8 kA
Rated conditional short-circuit current Icc with gl-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	263000 W
--	----------

Architecture

Number of poles	4
Control/operation element	Long rotary handle
Type of pole	4P

Installation, mounting

Nominal tightening torque	20 - 26 Nm
---------------------------	------------

Controls and indicators

Motor drive integrated	No
------------------------	----

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Total power loss under IN	43.20 W
---------------------------	---------

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Connection

Cross-section rigid conductor	185 - 240 mm ²
-------------------------------	---------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes