



HI454

Change-over switch 4P 250A

Technical Features

Voltage

Rated insulation voltage U_i	1000 V
Rated impulse withstand voltage U_{imp}	12000 V

Electric current

Rated current	250 A
Rated short-time withstand current I_{cw} IEC 60947	15 kA
Rated conditional short-circuit current I_{cc} with gI-gG fuses	50 kA

Power

Rated operational power under 400 V AC AC1	164000 W
--	----------

Architecture

Number of poles	4
Control/operation element	Long rotary handle
Type of pole	4P

Dimensions

Height	160 mm
Width	312 mm
Depth	218 mm

Controls and indicators

Motor drive integrated	No
------------------------	----

Cover, door

Interlockable	Yes
---------------	-----

Safety

Ingress Protection (IP) class	IP00
-------------------------------	------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Capacity

Number of modules	10
-------------------	----

Power

Total power loss under I_N	23.60 W
------------------------------	---------

Connection

Cross-section rigid conductor	95 - 150 mm ²
-------------------------------	--------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes