



JG220U

**IP66 32A 2P UTILITY ISOLATOR**

**Technical Features**

**Architecture**

Number of poles	2
Type of pole	1P+N

**Electric current**

Rated current	32 A
Acceptable current rating AC21 category A	32 A
Acceptable current rating AC22 category A	32 A

**Voltage**

Rated operational voltage Ue	250 - 250 V
------------------------------	-------------

**Electric current**

Rated short-circuit making capacity Icm under 240 V AC according to IEC 60947-3	0.38 kA
---	---------

**Voltage**

Rated insulation voltage Ui	250 V
-----------------------------	-------

**Electric current**

Rated short-time withstand current Icw t=1 S 220 - 240 V AC according to IEC 60947 - 3	0.38 kA
--	---------

**Installation, mounting**

Nominal tightening torque	2.50 - 2.50 Nm
---------------------------	----------------

**Dimensions**

Height	170 mm
Width	84 mm
Depth	87 mm

**Safety**

Ingress Protection (IP) class	IP66
-------------------------------	------

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

**Connection**

Cross-section rigid conductor	6 - 10 mm <sup>2</sup>
-------------------------------	------------------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Sustainability**

RoHS conform	Yes
--------------	-----