



TYA664BN



DIMMER 4 CHANNELS 600W WITH PARALLELIZATION

Technical Features

Voltage

Operating voltage over bus	21 - 32 V
Input voltage	230 - 230 V
System supply voltage	30 V DC Via bus
Auxiliary tension	230 - 230 V

Electric current

Bus current consumption data transfer	2.40 mA
---------------------------------------	---------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Connection

Cross-section flexible conductor	0.75 - 2.5 mm ²
Cross-section rigid conductor	0.75 - 2.5 mm ²

Equipment

Number of outputs	4
-------------------	---

Lighting

LED lamp power	480 W
----------------	-------

Equipment

Type of dimmer	Dimming actuator
----------------	------------------

Capacity

Number of modules	10
-------------------	----

Power

230 V incandescent and halogen lamp	600 W
Power incandescent lamp	5 - 600 W
Power of variator	5 - 600 W

Connectivity

With bus system KNX radio	No
Type of connection	quickconnect

Lighting

Dimmable 230 V LED lamp	120 - 120 W
-------------------------	-------------

Settings

Supported configuration mode	ETS
------------------------------	-----

Texts

Fuse	Overheating protection (display using LEDs) Short-circuit proof and overload-proof (display using LEDs)
Operating mode	Load coupling of 4 channels to increase output power using parallel connection of the outputs
Dimming principle	Phase cut-on or cut-off according to load type, self-learning Minimum/maximum dimming values per channel settable on device
Function	Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus
Type of connection	With quickconnect plug-in terminals
Labelling	Large labelling field
Protection	With overheating, overload and short-circuit protection