



47508989

**SCHUKO soc. out., S.1/B.3/B.7, p. white glossy**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	Yes
---------------------	-----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

---

**Texts**

Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	With labelling field

---

**Suitable for**

S.x/B.x

---

**Sustainability**

Halogen free	Yes
RoHS conform	Yes