Product Datasheet
TYF642F



TYF642F

Fancoil 2 outputs 10A, hand status, KNX

Technical Features

Connectivity

With bus system KNX radio	No

Voltage

Operating voltage over bus	21 - 32 V
Auxiliary tension	230 - 230 V

Electric current

Max. switching current	10 A

Use conditions

Operating temperature	-5 - 45 °C

Connection

Cross-section flexible conductor	0.75 - 4 mm^2
Cross-section rigid conductor	1.5 - 4 mm^2

Dimensions

Number of width units	4

Texts

Type of connection	With screw terminals

Data act compliance

Is generating data	Yes
Data types	Basic information Fan coil control Scenes
Data formats	KNX (TP)
Estimated daily data volume	10 KB - 100 KB
Real time data generation	Yes
Data stored on device	No

Sustainability

REACh-SVHC free	Yes
RoHS conform	Yes