



WGCS115S

15A SINGLE SWITCHED SOCKET

Technical Features

Electric current

Rated current	15 A
Output current	0 mA

Voltage

Rated voltage	250 V
Nominal voltage	220-250 V
Output voltage	0-0 V

Use conditions

Operating temperature	-20-45 °C
-----------------------	-----------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Output power	0 W
Power consumption standby	0 W

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	34 mm
Width	86 mm
Depth	22 mm
Built-in depth flush-mounted boxes	35 mm
Built-in depth	22 mm

Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm ²

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	None

Capacity

Number of modules	0
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Suitable for

shark	
-------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes