



VANR1201

supply-unit R12 for wet-cleaned floors for mounting of tube cable outlet alu

**Technical Features**

**Architecture**

With carpet protection frame	Yes
With opening carpeting	No

**Dimensions**

Built-in depth	90 mm
Built-in diameter	306 mm
Outer diameter	325 mm

**Configuration**

Installation size (underfloor installations)	R12
--	-----

**Installation, mounting**

Suitable for recessed floor mounting	No
Suitable for concrete installation	Yes
Suitable for outdoor usage	No
Suitable for raised floor installation	No
Suitable for wet cleaning	Yes

**Instructions**

Floor maintenance	Wet
-------------------	-----

**Materials**

Material	Aluminium
----------	-----------

**Use conditions**

Vertical load applied across large surface area (heavy load)	10 kN
Vertical load applied across small surface area	3 kN

**Functions**

Suitable for sub-floor duct	No
-----------------------------	----

**Shape**

Shape	Round
-------	-------

**Texts**

Cable outlet	With cable outlet in cover
--------------	----------------------------

**Materials**

Colour	Aluminium
--------	-----------

**Connection**

Number of conduit inlets	3
Number of sockets SCHUKO	12

**Equipment**

Number of built-in devices	12
Number of outlet boxes	3

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK10
Protection class in unused condition	IP66

Illustrations | Drawings

