



VML1010

**Dual Row 18+20W 100A Switch 2\*100A 30mA RCCB**

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Architecture**

Number of poles 2

**Functions**

Has protection main switch Yes

**Capacity**

Number of modules 38

**Electric current**

Rated current 100 A

**Dimensions**

Depth 100 mm

Height 485 mm

Width 476 mm

**Cover, door**

Interlockable No

Door/cover is transparent No

**Materials**

RAL code 9010

Colour Pure white

Material Steel

**Connection**

Number of accessible phases 2

**Scope of delivery**

Number of earth leakage circuit breaker type A 2

Number of RCCB in enclosure 2

**Equipment**

Number of rows 2

Number of rails 2

With socket outlet No

**Safety**

Ingress Protection (IP) class IP2XC

**Sustainability**

RoHS conform Yes