



WGDL131NP-12VIG

12V 3G press switch with led;ig

Technical Features

Electric current

Switching current 10 A

Voltage

Rated voltage 250 V

Architecture

Control/operation element Double rocker

Materials

Colour Interstellar grey

Surface finish Matt

Treatment Varnished

Transparent No

Dimensions

Height 90 mm

Width 90 mm

Depth 25 mm

Controls and indicators

Number of buttons 3

Connectivity

Type of connection Screw terminal

Safety

Ingress Protection (IP) class IP20

Texts

Switch mode 1-way

Suitable for

shark

Sustainability

RoHS conform Yes