



WGML113AS

10AX 1G intermediate switch;as

Technical Features

Electric current

Switching current 10 AX (100W LED (SBL))

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Frequency

Frequency 50-60 Hz

Materials

Colour Aurora silver

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Identification

Assembly arrangement Surface-mounted frame

Connectivity

Mounting type Screw mounting

With claw mounting No

Controls and indicators

Number of buttons 1

Dimensions

Dimensions 86 x 86 mm

Built-in depth 25 mm

Built-in depth flush-mounted boxes 35 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Electric current

Rated current 10 A

Connection

Type of contacts 1 W + neutral

Connector/plug type Screw terminal

Texts

Switch mode Intermediate

Sustainability

RoHS conform Yes