



BD340

**Earth leakage add-on block 3P 40A 30mA A high immunity Class**

**Technical Features**

**Electric current**

Rated current	40 A
Rated residual operating current I <sub>dn</sub>	30 mA

**Architecture**

Number of poles	3
-----------------	---

**Safety**

Residual current type	A HI
-----------------------	------

**Capacity**

Number of modules	3
-------------------	---

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Installation, mounting**

Nominal tightening torque	2.80 - 2.80 Nm
---------------------------	----------------

**Power**

Total power loss under I <sub>N</sub>	3.8 W
---------------------------------------	-------

**Endurance**

Electric endurance in number of cycles	2000
Number of mechanical operations	1000

**Voltage**

Rated insulation voltage U <sub>i</sub>	500 V
Rated impulse withstand voltage U <sub>imp</sub>	4000 V

**Connection**

Cross-section of input and output with screws, for massive conductors	1 - 25 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	1 - 16 mm <sup>2</sup>

**Connectivity**

Down connection alignment for modular devices	Aligned terminal
---	------------------

**Dimensions**

Height	70 mm
Width	35 mm
Depth	92 mm

Illustrations | Drawings

