



29538982



LED signal light, white lighting, S.1, white glossy

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Lighting

| | |
|--------------|-----|
| Type of lamp | LED |
|--------------|-----|

Materials

| | |
|----------------|------------------|
| Colour | White |
| RAL code | 1013 |
| Surface finish | Glossy |
| Material | Metal Plastic |
| Treatment | Untreated |

Dimensions

| | |
|--------|-------|
| Height | 70 mm |
| Width | 70 mm |
| Depth | 50 mm |

Connection

| | |
|-------------------------|-----------------------------|
| Conductor cross-section | 2.50 - 2.50 mm ² |
|-------------------------|-----------------------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|-----------|--|
| Lighting | Light colour cold white |
| Labelling | Foils with imprint of symbols insertable |
| Imprint | Without imprint |

Suitable for

| | |
|---------|--|
| S.x/B.x | |
|---------|--|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |