



WGML113KB

**10AX 1G intermediate switch;kb**

**Technical Features**

**Electric current**

Switching current	10 AX (100W LED (SBL))
-------------------	------------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Voltage**

Rated voltage	250 V
---------------	-------

**Frequency**

Frequency	50-60 Hz
-----------	----------

**Materials**

Colour	Knight black
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished

**Identification**

Assembly arrangement	Surface-mounted frame
----------------------	-----------------------

**Connectivity**

Mounting type	Screw mounting
With claw mounting	No

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	86 x 86 mm
Built-in depth	25 mm
Built-in depth flush-mounted boxes	35 mm

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Architecture**

Control/operation element	Single rocker
---------------------------	---------------

**Electric current**

Rated current	10 A
---------------	------

**Connection**

Type of contacts	1 W + neutral
Connector/plug type	Screw terminal

**Texts**

Switch mode	Intermediate
-------------	--------------

**Sustainability**

RoHS conform	Yes
--------------	-----