



TYB708D



**Universal interface 8gang comfort**

**Technical Features**

**Settings**

Supported configuration mode ETS

**Electric current**

Number of entry circuits 8

**Equipment**

External signal voltage necessary Yes

**Connectivity**

With bus system KNX radio No

**Equipment**

Radio frequency bidirectional No

With battery No

**Installation, mounting**

Mounting on Flush mounting

**Lighting**

LED controlling Yes

**Materials**

Colour Black

RAL code 9005

**Safety**

Ingress Protection (IP) class IP20

**Use conditions**

Operating temperature -5 - 45 °C

**Cable**

Cable length 10 m

**Voltage**

Input voltage 20 - 20 V

Operating voltage over bus 21 - 32 V

Type voltage supply DC

System supply voltage 30 V DC Via bus

**Dimensions**

Depth 32 mm

**Texts**

Type of connection With screw terminals

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes