



382120



Switch f.blinds 1p f.lock cyl.,earth contact,neut. p.,splash-prot. flushmtd IP44

Technical Features

Controls and indicators

Venetian blind switch type 1-pole switch

Materials

Material Metal
Plastic
Treatment Untreated

Voltage

Rated voltage 250 V

Electric current

Switching current 10 AX (100W LED (SBL))
Switching current 10 A

Safety

Ingress Protection (IP) class IP44

Texts

Switch mode 1-pole
With neutral position
Type of connection With screw terminals
Installation mode For screw fastening
Without spreader claws

Suitable for

B.3 / B.7 / K.1 / K.5 / Q.1 / Q.3 / Q.7 / R.1 / R.3 / R.8 / S.1

Sustainability

Halogen free Yes
REACH-SVHC free Yes
RoHS conform Yes