



WRDP50NPSW

### 50A Double Pole Switch 1 Gang with LED Indicator Polished Steel White Insert

#### Technical Features

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

#### Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Dimensions	86 x 86 mm
Built-in depth	20.20 mm

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Electric current

Rated current	50 A
---------------	------

#### Texts

Lighting	With control LED for ON
Switch mode	2-pole

#### Sustainability

RoHS conform	Yes
--------------	-----