



47753532



SCHUKO soc.out. 2gang hor. hinged cover surface-mtd, W.1, p.white, matt, plastic

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Use conditions

Operating temperature -15 - 30 °C

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white
RAL code 9010
Surface finish Matt
Material Thermoplastic
Treatment Untreated

Dimensions

Height 76 mm
Width 147 mm
Depth 63 mm
Built-in depth flush-mounted boxes 0 mm
Height of P-touch band for labelling field 12 mm

Connection

Connector/plug type Plug-in terminal
Conductor cross-section 1.0 - 2.5 mm²

Installation, mounting

Mounting on Surface mounting

Connectivity

Type of connection Plug-in connection
Mounting type Screw mounting

Equipment

Connector/plug type socket outlet SCHUKO
Rotated central insert No
With hinged lid Yes
With round protective earth pin No
With signal lamp No
With lock No

Accessories

Has labelling field Yes

Cover, door

Type of lid Self-closing hinged cover, can be arrested in end position

Capacity

Number of modules 2

Safety

With enhanced contact protection No
Impact resistance IK IK05
Ingress Protection (IP) class IP55

Functions

With orientation lighting No

Functions

With function lighting	No
------------------------	----

Identification

With imprint	No
--------------	----

Texts

Cover	Complete housing
-------	------------------

Wiring	Inserts wired-through
--------	-----------------------

Protection	Without enhanced contact protection
------------	-------------------------------------

Type of connection	With plug-in terminals
--------------------	------------------------

Labelling	With labelling field
-----------	----------------------

Terminal	With Wago clip-in 2-wire connection terminal for wiring With two clip-in places for Wago 2-wire connection terminals in the housing floor
----------	----------------------------------------------------------------------------------------------------------------------------------------------

Sustainability

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----