



KB480B

Insulated busbar 3P+N 80A prong 16mm<sup>2</sup> 57M

Technical Features

Electric current

Rated current	80 A
---------------	------

Architecture

Number of poles	4
-----------------	---

Dimensions

Length	1000 mm
--------	---------

Voltage

Rated impulse withstand voltage Uimp	4000 V
Rated operational voltage Ue	230 - 400 V

Connection

Cross-section rigid conductor	16 mm <sup>2</sup>
Connector/plug type	Phase busbar with pin

Capacity

Number of modules	57
-------------------	----

Sustainability

RoHS conform	Yes
--------------	-----