



382210



Switch for blinds 2pole for lock cylinder, blind control

Technical Features

Controls and indicators

Venetian blind switch type 2-pole switch

Materials

Surface finish Matt
 Material Metal
Plastic
 Treatment Untreated

Voltage

Rated voltage 250 V

Electric current

Switching current 10 AX (100W LED (SBL))
 Switching current 10 A

Safety

Ingress Protection (IP) class IP20

Texts

Switch mode With neutral position
 Type of connection With screw terminals
 Installation mode For screw fastening
Without spreader claws

Suitable for

B.3 / B.7 / K.1 / K.5 / Q.1 / Q.3 / Q.7 / R.1 / R.3 / R.8 / S.1

Sustainability

Halogen free Yes
 REACh-SVHC free Yes
 RoHS conform Yes