



20346086

Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,Q1/3,ant.

Technical Features

Electric current

Rated current	10 A
Switching current	10 A

Voltage

Nominal voltage	230 - 230 V
Rated voltage	230 V

Frequency

Frequency	50 - 60 Hz
-----------	------------

Settings

Comfort temperature setpoint	10 - 50 °C
------------------------------	------------

Materials

Colour	Anthracite
RAL code	7016
Surface finish	Velvety
Material	Metal Plastic
Treatment	Varnished

Dimensions

Height	71 mm
Width	71 mm
Depth	60 mm

Screen

With display	No
--------------	----

Equipment

Switching temperature difference	1 K
Type of thermostat	Regulator of heating floor
Type of probe	Bimetal

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Connection

Type of contacts	1NO
------------------	-----

Use conditions

Energy efficiency class	I (1%)
-------------------------	--------

Texts

Installation mode	Without spreader claws
Type of connection	With plug-in terminals
Thermal re-circulation	With thermal return
Imprint	With imprint
Junction	With separate connection for night lowering

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes