



20346086

Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,Q1/3,ant.

**Technical Features**

**Architecture**

Control/operation element Rotative

**Electric current**

Rated current 10 A

Max. switching current 10 A

**Voltage**

Nominal voltage 230 - 230 V

**Power supply**

Supply voltage 230 V AC

**Frequency**

Frequency 50 - 60 Hz

**Settings**

Comfort temperature setpoint 10 - 50 °C

**Materials**

Colour Anthracite

RAL code 7016

Surface finish Velvety

Material Metal  
Plastic

**Dimensions**

Height 71 mm

Width 71 mm

Depth 54.5 mm

**Screen**

With display No

**Equipment**

Switching temperature difference 1 K

Type of thermostat Regulator of heating floor

Type of probe Floor heating probe

**Safety**

Ingress Protection (IP) class IP20

**Connection**

Type of contacts 1NO

**Compatibility**

Type of HVAC control Heating

**Use conditions**

Energy efficiency class I (1%)

**Texts**

Installation mode Without spreader claws

Type of connection With plug-in terminals

Thermal re-circulation With thermal return

Imprint With imprint

Junction With separate connection for night lowering

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes