



47087009



SCHUKO soc.out. residual current circuit-breaker,enhncd contact prot.,K.1,wh.gl.

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 16 A

Frequency

Frequency 50 - 60 Hz

Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth 31.90 mm

Installation, mounting

Mounting on Flush mounting

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting
Claw mounting

Equipment

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

Accessories

Has labelling field No

Capacity

Number of modules 1

Safety

With enhanced contact protection Yes

Impact resistance IK IK07

Ingress Protection (IP) class IP20

Functions

With orientation lighting No

With function lighting No

Identification

With imprint No

Texts

Cover Central cover plate

Protection Enhanced contact protection

Texts	
Type of connection	With plug-in terminals
Type	Type A for alternating currents and pulsating direct currents

Suitable for	
K.x	

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes