



47087004



**SCHUKO soc.out. residual current circuit-breaker,enhncd contact prot.,K5,steel,**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Stainless steel

RAL code 9022

Surface finish Matt

Material Metal  
Plastic  
Stainless steel

Treatment Varnished

**Dimensions**

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth 31.90 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Screw mounting  
Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection Yes

Impact resistance IK IK07

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Central cover plate

Protection Enhanced contact protection

---

**Texts**

Type of connection	With plug-in terminals
Type	Type A for alternating currents and pulsating direct currents

---

**Suitable for**

K.x

---

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes